
Precision DC Source

 $DC205 - \pm 100 VDC$ source



- ±100 VDC range
- · True 6-digit resolution
- 1 ppm/°C stability
- 0.0025 % accuracy (1 yr.)
- Triggerable voltage scans
- · Low-noise design
- · Linear power supply
- · RS-232, USB and fiber optic interfaces
- · DC205 ... \$1995 (U.S. list)

DC205 Precision DC Source


The DC205 low-noise, high-resolution DC voltage source is the right tool when a precision bias source is needed. Its bipolar, four-quadrant output delivers up to 100 V with 1 μ V resolution and up to 50 mA of current. In 4-wire mode (remote sense), the instrument corrects for lead resistance delivering accurate potential to your load. The DC205's output stability is a remarkable ± 1 ppm over 24 hours. With its linear power supply, there is no need to worry about high-frequency noise.

True 6-Digit Resolution

The front-panel display of the DC205 lets you set voltage with true 6-digit resolution. There are three voltage ranges to choose from: $\pm 1~V$, $\pm 10~V$ and $\pm 100~V$ which allows voltage settings from 1 μV to 100~V— eight orders of magnitude!

Low-Noise Design

The DC205 has outstanding noise characteristics — on the 1 V range, the rms noise is less than 1 μV (0.1 Hz to 10 Hz). It is also accurate to 0.0025 % over a one year period, and it has excellent temperature stability with a specification of less than 1 ppm/°C. The design even features linear power supplies rather than switching power supplies, so switching frequency interference can never be a problem.



DC205 Stability

Voltage Scanning

The instrument's triggerable voltage scanning feature can be useful in a number of experimental applications. The start and stop voltage, and scan speed can all be controlled. Scan speeds can be set from 100 ms to 10,000 s, and the scan function can either be a ramp or a triangle wave. Single scans and continuous scans are both supported, and the instrument can be triggered from the front panel, remotely over one of the interfaces, or from an external trigger signal.

Bipolar, Four-Quadrant Output

The DC205 can output either positive or negative voltages, and it operates in either grounded or floating mode. In floating mode, the output can float up to 250 V relative to chassis ground. You can also select either 2-wire or 4-wire operation. In 4-wire mode (remote sense), the instrument maintains its preset voltage directly at your load eliminating the effect of lead resistance.

Computer Interfaces

The DC205 has both RS-232 and USB computer interfaces on its rear panel. All functions of the instrument can be set or read via the interfaces. For remote interfacing with complete electrical isolation, the DC205 also has a rear-panel fiber optic interface. When connected to the SX199 Remote Computer Interface Unit, a path for controlling the DC205 via GPIB, Ethernet, and RS-232 is provided.



DC205 front panel



DC205 rear panel



DC205 Specifications

Signal Output

Output configuration 2-wire or 4-wire (remote sense)

> Output can be set to Ground or Float (250 V max.) mode

±1 VDC range

Full scale $\pm 1.010000 \, V$ Resolution $1 \mu V$ Max. current 50 mA

24 hour: $\pm (7 \text{ ppm of setting} + 2 \mu \text{V})$ Accuracy

90 day*: $\pm (12 \text{ ppm of setting} + 6 \mu\text{V})$ 1 year*: \pm (25 ppm of setting + 10 μ V)

24 hour: $\pm (1 \text{ ppm of setting} + 1 \mu \text{V})$ Stability $\pm (1 \text{ ppm of setting} + 1 \mu V)/^{\circ}C$ Temp. coefficient

 $(0 \,^{\circ}\text{C to } 40 \,^{\circ}\text{C})$

Noise (typ.) $0.5 \,\mu Vrms \, (0.1 \,Hz \,to \,10 \,Hz)$

 $9 \mu Vrms (10 Hz to 100 kHz)$

±10 VDC range

±10.10000 V Full scale Resolution $10 \,\mu V$ Max. current 50 mA

24 hour: $\pm (7 \text{ ppm of setting} + 12 \mu\text{V})$ Accuracy

90 day*: $\pm (12 \text{ ppm of setting} + 20 \mu\text{V})$ 1 year*: $\pm (25 \text{ ppm of setting} + 20 \mu\text{V})$

24 hour: $\pm (1 \text{ ppm of setting} + 3 \mu \text{V})$

Stability Temp. coefficient $\pm (1 \text{ ppm of setting} + 2 \mu V)/^{\circ}C$

(0°C to 40°C)

Noise (typ.) $1.5 \,\mu\text{Vrms}$ (0.1 Hz to 10 Hz)

12 μVrms (10 Hz to 100 kHz)

±100 VDC range

Full scale $\pm 101.0000 \, V$ Resolution $100 \,\mu V$ 25 mA Max. current

24 hour: \pm (8 ppm of setting + 120 μ V) Accuracy

90 day*: \pm (12 ppm of setting + 200 μ V) 1 year*: \pm (25 ppm of setting + 200 μ V)

Stability 24 hour: \pm (1 ppm of setting $+20 \mu V$)

 $\pm (1 \text{ ppm of setting} + 15 \,\mu\text{V})/^{\circ}\text{C}$ Temp. coefficient

 $(0 \,^{\circ}\text{C to } 40 \,^{\circ}\text{C})$

Noise (typ.) $12 \,\mu\text{Vrms} (0.1 \,\text{Hz to} \, 10 \,\text{Hz})$

50 μVrms (10 Hz to 100 kHz)

Voltage Scanning

Scan speed 0.1 s to 9999.9 s

Scan type Ramp or triangle wave, continuous

or single shot

Triggered scans Scans can be triggered using the

rear-panel trigger input

Remote Interfaces

USB Virtual COM port with FTDI

> drivers, 115.2k baud, 8 bits, no parity, 1 stop bit, RTS/CTS flow

DB-9 connector, 9600 baud

RS-232 Optical fiber Connection to SX199 Optical

> Interface Controller. Provides connectivity to GPIB, RS-232 and

Ethernet

General

Operating temperature 0°C to 40°C, non-condensing

Power <30 W, 100/120/220/240 VAC,

50 Hz or 60 Hz

Dimensions 8.3" × 3.55" × 13.0" (WHD)

Weight

Warranty One year parts and labor on defects

in materials and workmanship

* Preliminary specifications

All performance specifications after 2 hours warm-up at

23 °C±1 °C ambient, unless otherwise stated

Ordering Information

DC205 \$1995 Precision voltage source O205RMS Single rack mount kit \$100 O205RMD Dual rack mount kit \$100

